








NOTES


- (1) MATERIAL: SUS-301 THICKNE=0.08mm
- (2) PRODUCT SPECIFICATIONS:
 - 2-1: RATED CURRENT: 2.0A
 - 2-2: VOLTAGE RATING: 10.0V
 - 2-3: CONTACT RESISTANCE: 30mΩ/MAX
 - 2-4: WELDING THRUST: ≥3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6: DURABILITY: 1500 CYCLES
- (3): SALT SPRAY: 24 HOURS
- (4): FINISH: 1.25~7.6um" NICKEL UNDERPLATING OVER ALL.
- (5): REQUIREMENTS
 - 5-1: TERMINAL TO EAT FULL TIN, NOT PEELING
 - WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)



METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)



STATED AT COMPRESSION
(FOR REFERENCE ONLY)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5'		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L1.70*W1.00*H1.80	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-TXT171018A
				MOLD NO.	
		APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2412191631
				SHEET NO.	1 OF 1