






3D VIEW




- 1.MATERIAL SPECIFICATION:
1.1.YCUT-FX-EH T=0.08±0.005MM
2.TEST REQUIREMENTS:
2.1.CONTACT RESISTANCE: 80mΩ MAX
2.2.VOLTAGE RATING: 1.5 V/AC/DC/MAX
2.3.RATED CURRENT: 1.0A/MAX
2.4.WELDING THRUST: ±3.0Kg
2.5.DURABILITY: 1,500 TIMES
2.6.OPERATING TEMPERATURE: -20 ° ~ 80 ° C
3.PLATING REQUIREMENTS:
3.1.THE NICKEL-PLATED SUBSTRATE IS 50U MIN.
3.2.SALT SPRAY TEST TO MEET THE REQUIREMENTS OF 24 HOURS.
3.3.TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING, OBVIOUS COLOR AND OTHER ADVERSE
3.4.RHSS, REACH, HF HALOGEN-FREE AND A SERIES OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05



RECOMMENDED METAL MASK

TOLERANCE: ±0.05



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2. 20*W1.00*H1.90	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT221019	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412121006	
			SHEET NO. 1 OF 1	