

接点表

CN1	CN2
01	01
02	02
03	03
04	04
05	05
06	06
07	07
08	08
09	09
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
SHELL	SHELL

注:


- 100%短/断路&错线测试条件;
- 导通阻抗 $\leq 5\Omega$, 绝缘阻抗 $\geq 10M\Omega$. 高压测试, DC 300V/10mS.
- 产品采用PCB板连接, 符合1.4版技术规范.

5	外模	PVC胶料 45P 黑色		2.8G
4	内模	PE胶料 透明		1.2G
3	内连接	PCB板 T=1.6MM		1PCS
2	连接器	HDMI 19P A(F)(0.5) 铁壳镀镍 PIN针镀金		1PCS
1	连接器	HDMI 19P A(F)(0.5) 铁壳镀镍 PIN针镀金		1PCS
序号	名称	材料	物料编号	用量



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$ 

UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

HDMI 母转母 180° 外露带耳款

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW13-HDMI-280B

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2405230940

SHEET NO.

1 OF 1