



PIN ASSIGNMENT

HDB15F	HDB15F
1	1
2	2
3	3
4	4
5	5
6	6
7	7
...	...
14	14
15	15

Specification:

Rating Current: 3 AMP

Insulation Resistance: 1000M Ohm min. at 500V DC

Dielectric Strength: 1000V AC for one minute.

Temperature: -55°C~+105°C

Contact: Brass Gold flash over Nickel Plated

Shell: SPCC Nickel Plated

Insulator: PBT+30%GF Blue

Screw: Steel 12L14 Nickel Plated

Label: Yellow color black charactor

One Side: MINI GENDER CHANGER

Other Side: U.S.A. PATENT 5199906 GENDER CHANGER



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2° X.X* ±0.5°		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDB15F TO HDB15F	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW02-HDB-178B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2211081442
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1