







NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



P.C.B LAYOUT

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	PIN	A	B	C
DMX-2PWT-43	2	1.25	7.50	
DMX-3PWT-43	3	2.50	8.75	
DMX-4PWT-43	4	3.75	10.00	2.50
DMX-5PWT-43	5	5.00	11.25	3.75
DMX-6PWT-43	6	6.25	12.50	5.00
DMX-7PWT-43	7	7.50	13.75	6.25
DMX-8PWT-43	8	8.75	15.00	7.50
DMX-9PWT-43	9	10.00	16.25	8.75
DMX-10PWT-43	10	11.25	17.50	10.00
DMX-11PWT-43	11	12.50	18.75	11.25
DMX-12PWT-43	12	13.75	20.00	12.50
DMX-13PWT-43	13	15.00	21.25	13.75
DMX-14PWT-43	14	16.25	22.50	15.00
DMX-15PWT-43	15	17.50	23.75	16.25
DMX-16PWT-43	16	18.75	25.00	17.50

TOLERANCE				 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	±0.30	X.*	±5°	PART NO. DMX-XPWT-43	TITLE: WAFER 1.25 贴片		
.XX	±0.20	X.X*	±3°				
.XXX	±0.10	X.XX*	±1°				
UNITS		mm		DESIGN:	Ethan		
MATERILA		— — —		CHED:	Olvia		
FINISH		— — —		APPD:	Ava		
						SCALE	SHEET
						N:A	1/1