







NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 0.8
- 2.Voltage Rating: 30V AC DC
- 3.Current Rating: 0.5A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 200V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



P.C.B LAYOUT

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PDrt No	Pin	D	B
D08-2PWT-43	2	0.80	3.85
D08-3PWT-43	3	1.60	4.65
D08-4PWT-43	4	2.40	5.45
D08-5PWT-43	5	3.20	6.25
D08-6PWT-43	6	4.00	7.05
D08-7PWT-43	7	4.80	7.85
D08-8PWT-43	8	5.60	8.65
D08-9PWT-43	9	6.40	9.45
D08-10PWT-43	10	7.20	10.25
D08-11PWT-43	11	8.00	11.05
D08-12PWT-43	12	8.80	11.85
D08-13PWT-43	13	9.60	12.65
D08-14PWT-43	14	10.40	13.45
D08-15PWT-43	15	11.20	14.25
D08-16PWT-43	16	12.00	15.05
D08-17PWT-43	17	12.80	15.85
D08-18PWT-43	18	13.60	16.65
D08-19PWT-43	19	14.40	17.45
D08-20PWT-43	20	15.20	18.25
D08-21PWT-43	21	16.00	19.05
D08-22PWT-43	22	16.80	19.85
D08-23PWT-43	23	17.60	20.65
D08-24PWT-43	24	18.40	21.45

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO. D08-XPWT-43	TITLE: WAFER 0.8 贴片	
.XX ±0.20	X.* ±3°		MANUFACTURE DWG	
.XXX ±0.10	X.XX* ±1°			
UNITS	mm	DESIGN: Ethan		
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1