




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




P/N	H
TS-1187A-S16	1.5
TS-1187B-S16	1.6
TS-1187C-S16	1.7
TS-1187D-S16	2.0
TS-1187E-S16	2.5
TS-1187F-S16	3.0
TS-1187G-S16	3.5
TS-1187H-S16	4.0
TS-1187I-S16	4.5
TS-1187J-S16	5.0

主要技术参数、性能


The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 travel	0.2±0.1mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min
工作温度 Operating temperature	-30°C~+80°C



电路图

CIRCUIT DIAGRAM



PCB.焊接图

PCB.WELDING DRAWING

E	按钮	黄铜	1	酸洗
D	盖板	不锈钢	1	清洗
C	防尘膜	聚酰亚胺	1	橙黄色
B	弹片	不锈钢	1	镀银
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.X:±0.35	X.X':±3"	PART NO.		TITLE:		
X.XX:±0.25	X.XX':±2"	TS-1187X-S16		TACT SWITCH		
X.XXX:±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	1/1