

强能电气有限公司

铜制电缆防水接头（IP68、CE、RoHS、无卤素）



强能型号 标准螺牙	线缆范围 mm	螺纹外径 mm	螺纹长度 mm	扳手尺寸 螺母/螺帽	铜电缆接头	备 注
PG7S	3-6.5	12.5	7	14/14	2.40	
PG7	4-8	12.5	8	17/17	3.31	
PG9	4-8	15.2	8	18/18	3.60	
PG11	5-10	18.6	9	22/22	4.60	
PG13.5	6-12	20.4	9.5	24/24	5.26	
PG16	9-14	22.5	9.5	25/25	6.25	
PG21	13-18	28.3	12	30/30	9.18	
PG29	18-25	37	12.5	40/40	16.12	
PG36	24-30	47	15	50/50	26.68	
PG42	31-41	54	15	59/59	37.50	
PG48	35-45	59.3	17	67/65	58.75	
M8×1.25	2-3.8	8	5.5	13/13	2.40	
M10×1.5	3-6.5	10	6.5	14/14	2.40	
M12S	3-6.5	12	7	14/14	2.40	
M12	4-8	12	8	17/17	3.31	
M16S	4-8	16	9	18/18	3.60	
M16	5-10	16	9	22/22	4.60	
M20S	6-12	20	9.5	24/24	5.26	
M20	9-14	20	9.5	25/25	6.25	
M25	13-18	25	12	30/30	9.18	
M32	18-25	32	12.5	40/40	16.12	
M40	24-30	40	15	50/50	26.68	

M50	31-41	50	15	59/59	37.50	
M63	35-45	63	17	67/65	58.75	
M63 大号	44-51	63	17	73/73	68.75	

备注：以上铜电缆防水接头型号，如需要加厚小孔线缆范围的，请另外咨询我们。谢谢！

- 1) 以上价格不含税和运费，开票另加 12%
- 2) 材质：优质黄铜镀镍；三元乙丙耐候橡胶
尼龙 PA66（UL 认证材料）；
- 3) 报价有效期为 2 个月
- 4) 电话：0577-61679080