



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
CXHP-2N-JK	2	2.50	5.70	3.70	3.70
CXHP-3N-JK	3	5.00	8.20	6.20	6.20
CXHP-4N-JK	4	7.50	10.70	8.70	8.70
CXHP-5N-JK	5	10.00	13.20	11.20	11.20
CXHP-6N-JK	6	12.50	15.70	13.70	13.70
CXHP-7N-JK	7	15.00	18.20	16.20	16.20
CXHP-8N-JK	8	17.50	20.70	18.70	18.70
CXHP-9N-JK	9	20.00	23.20	21.20	21.20
CXHP-10N-JK	10	22.50	25.70	23.70	23.70
CXHP-11N-JK	11	25.50	28.20	26.20	26.20
CXHP-12N-JK	12	27.50	30.70	28.70	28.70
CXHP-13N-JK	13	30.00	33.20	31.20	31.20
CXHP-14N-JK	14	32.50	35.70	33.70	33.70
CXHP-15N-JK	15	35.50	28.20	36.20	36.20
CXHP-16N-JK	16	37.50	40.70	38.70	38.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±1*	PART NO. CXHP-XN-JK	TITLE: XH2.5MM HOUSING		
.XX ±0.20			MANUFACTURE DWG		
.XXX ±0.10		DESIGN: Ethan			
UNITS	mm	CHED: Olivia			
MATERILA	— — —	CHPD: Ava			
FINISH	— — —	APPD: Ava			
			SCALE N:A	SHEET 1/1	

