



强能电气

金属电缆防水接头

序号	选购型号	范围mm	含螺母	不含螺母	包装/袋
2	BCGL- M10	3-6.5	1.37	1.22	
3	BCGL- M12	3-6.5	1.37	1.22	
4	BCGL- M12-8	4-8	1.89	1.74	
5	BCGL- M14	4-8	1.89	1.74	
6	BCGL- M16	4-8	2.00	1.80	
7	BCGL- M16-10	5-10	2.31	2.11	
8	BCGL- M18	5-10	2.31	2.11	
9	BCGL- M18-12	6-12	2.63	2.43	
10	BCGL- M20	6-12	2.63	2.43	
11	BCGL- M20-14	10-14	3.05	2.85	
12	BCGL- M22	10-14	3.05	2.85	
13	BCGL- M22-16	12-16	4.52	4.32	
14	BCGL- M24	10-14	4.20	3.90	
15	BCGL- M24-16	12-16	4.52	4.22	
16	BCGL- M25-14	10-14	4.41	4.11	
17	BCGL- M25-16	12-16	4.73	4.43	
18	BCGL- M25-18	13-18	5.04	4.74	
19	BCGL- M27	13-18	5.04	4.74	
20	BCGL- M28	13-18	5.04	4.74	
21	BCGL- M30	13-18	6.30	5.90	
22	BCGL- M30-22	15-22	6.93	6.33	
23	BCGL- M32	15-22	6.93	6.33	
24	BCGL- M32-25	18-25	8.61	8.01	
25	BCGL- M33	15-22	7.14	6.54	
26	BCGL- M36	18-25	8.61	8.01	
27	BCGL- M37	18-25	8.61	8.01	
28	BCGL- M40-25	18-25	10.50	9.50	
29	BCGL- M40-30	22-30	11.03	10.03	
30	BCGL- M40-33	25-33	16.28	15.28	
31	BCGL- M42	22-30	11.03	10.03	
32	BCGL- M47	25-33	16.28	15.28	
33	BCGL- M48	25-33	16.28	15.28	

34	BCGL- M50	32-38	21.00	19.00	
35	BCGL- M50-44	37-44	34.65	32.65	
36	BCGL- M54	32-38	22.05	20.05	
37	BCGL- M60	37-44	31.50	28.50	
38	BCGL- M63	37-44	34.65	31.65	
1	BCGL- PG7	3-6.5	1.37	1.22	
2	BCGL- PG9	4-8	1.89	1.69	
3	BCGL- PG11	5-10	2.31	2.11	
4	BCGL- PG13.5	6-12	2.63	2.42	
5	BCGL- PG16	10-14	3.05	2.84	
6	BCGL- PG19	10-14	4.41	4.11	
7	BCGL- PG21	13-18	5.04	4.74	
8	BCGL- PG25	15-22	6.93	6.33	
9	BCGL- PG29	18-25	8.61	8.01	
10	BCGL- PG36	25-33	16.28	15.28	
11	BCGL- PG42	32-38	22.05	20.05	
12	BCGL- PG48	37-44	31.50	28.50	
1	BCGL- G1/4	3-6.5	1.84	1.69	
1	BCGL- G3/8	4-8	2.31	2.11	
1	BCGL- G1/2	6-12	2.73	2.53	
2	BCGL- G3/4	13-18	5.04	4.74	
3	BCGL- G1	18-25	8.93	7.93	
4	BCGL- G1-1/4	25-33	17.33	16.33	
5	BCGL- G1-1/2	32-38	24.15	22.15	
6	BCGL- G2	37-44	34.65	31.65	
1	BCGL-NP T1/4	3-6.5	1.84		
2	BCGL- NPT3/8	4-8	2.31		
3	BCGL- NPT1/2	6-12	2.73		
4	BCGL- NPT3/4	13-18	5.04		
5	BCGL- NPT1	18-25	8.93		
6	BCGL- T1-NP1/4	25-33	17.33		
7	BCGL- NPT1-1/2	32-38	24.15		
8	BCGL- NPT2	37-44	34.65		
注： NPT型 不含螺母					
注： 以上单价不含税运					