



技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
CXAP-02V-JK	2	2.50	5.70	3.70	3.70
CXAP-03V-JK	3	5.00	8.20	6.20	6.20
CXAP-04V-JK	4	7.50	10.70	8.70	8.70
CXAP-05V-JK	5	10.00	13.20	11.20	11.20
CXAP-06V-JK	6	12.50	15.70	13.70	13.70
CXAP-07V-JK	7	15.00	18.20	16.20	16.20
CXAP-08V-JK	8	17.50	20.70	18.70	18.70
CXAP-09V-JK	9	20.00	23.20	21.20	21.20
CXAP-10V-JK	10	22.50	25.70	23.70	23.70
CXAP-11V-JK	11	25.50	28.20	26.20	26.20
CXAP-12V-JK	12	27.50	30.70	28.70	28.70
CXAP-13V-JK	13	30.00	33.20	31.20	31.20
CXAP-14V-JK	14	32.50	35.70	33.70	33.70
CXAP-15V-JK	15	35.50	28.20	36.20	36.20
CXAP-16V-JK	16	37.50	40.70	38.70	38.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±1*	PART NO. CXAP-XV-JK	TITLE: XH2.5MM HOUSING		
.XX ±0.20			MANUFACTURE DWG		
.XXX ±0.10					
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1