




REV	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW VERSION	Toy	Jerry	2024/08/21

PIN	P/N	DIM(mm)	
		A	B
2X2	991-041-2143	3.00	9.65
2X3	991-061-2143	6.00	12.65
2X4	991-081-2143	9.00	15.65
2X5	991-101-2143	12.00	18.65
2X6	991-121-2143	15.00	21.65
2X7	991-141-2143	18.00	24.65
2X8	991-161-2143	21.00	27.65
2X9	991-181-2143	24.00	30.65
2X10	991-201-2143	27.00	33.65
2X11	991-221-2143	30.00	36.65
2X12	991-241-2143	33.00	39.65

Main Spec Specifications/主要技术参数

1. Material/材质:

Housing/塑胶: LCP, UL94 V-0; BLACK/黑色;
Pin/针脚: Brass, Sn-Plated/黄铜, 镀锡;
Tab/焊片: Brass, Sn-Plated/黄铜, 镀锡;

2. Rated Current/额定电流: 5.0A AC/DC;

3. Rated Voltage/额定电压: 250V AC/DC;

4. Contact Resistance/接触电阻: ≤10mΩ;

5. Insulation Resistance/绝缘阻抗: ≥1000MΩ;

6. Withstand Voltage/耐电压: 1000V AC/minute;

7. Temperature Range/工作温度: -25℃~+85℃

8. Order information/编码原则: 991-XX1-7143

Poles/线数

X± 0.35	X°± 5°	 Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司		
.X± 0.20	.X°± 3°			
.XX± 0.15	.XX°± /	TITLE: 3.0MM Pitch Wafer 180° SMT	PART NO. 991-XX1-2143	
.XXX± 0.10	.XXX°± /		DWG NO: C-991-XX1-2143	
UNITS:	mm	APPD:		SCALE N/A
The information in this document is property of JiDe company and should not be copied or reproduced in any other way, without written permission.		CHKD:		
		DRAW:		
			SHEET 1/2	REV. A0