








- Specifications:
- 1.Contact Resistance/接触电阻:≤20mΩ
 - 2.Insulation Resistance/绝缘电阻:≥100MΩ
 - 3.Rated Voltage/额定电压:100V Max AC/DC
 - 4.Rated Current/额定电流:3.0A Max AC/DC
 - 5.Withstand Voltage/耐压: 1000v Ac/minute
 - 6.Temperature Range/工作温度范围:-40℃~+85℃
 - 7.Housing/外壳:PPS UL94V-0 Grey
 - 8.Contacts/端子:Brass Sn-Plated
 - 9.RoHS Compliance/产品符合RoHS,

X± 0.35	X°± 5°	 Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司			
.X± 0.20	.X°± 3°				
.XX± 0.15	.XX°± /	TITLE: 2.20mm Pitch 12PIN Male 90°DIP			
.XXX± 0.10	.XXX°± /	PART NO. 991-121-5128			
UNITS: mm		DWG NO: C-991-121-5128			
The information in this document is property of JiDe company and should not be copied or reproduced in any other way, without written permission.		APPD:			
		CHKD:			
		DRAW:			
			SCALE	SHEET	REV.
			N/A	1/1	A0