





REV	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW	YUAN	RAY	2024/07/25

- Specifications:
- 1.Contact Resistance/接触电阻:≤20mΩ
 - 2. Insulation Resistance/绝缘电阻:≥100MΩ
 - 3.Rated Voltage/额定电压:100V Max AC/DC
 - 4. Rated Current/额定电流:3.0A Max AC/DC
 - 5. Withstand Voltage/耐压: 1000v Ac/minute
 - 6. Temperature Range/工作温度范围:-40℃~+85℃
 - 7. Housing/外壳:PPS UL94V-0 Grey
 - 8. Contacts/端子:Brass Sn-Plated
 - 9. RoHS Compliance/产品符合RoHS;

X. ± 0.50	X. ° ± 1°		Guangdong JiDe Precision Electronics Co., Ltd			
.X ± 0.30	.X° ± 0.5°		广东济德精密电子有限公司			
.XX ± 0.20	.XX° ± /					
.XXX ± 0.15	.XXX° ± /					
UNITS:	mm					
The information in this document is property of JiDC company and should not be copied or reproduced in any other way, without written permission.		TITLE:	PART NO.			
		2.20mm Pitch 20PIN Male 90° DIP		991-201-5128		
		APPD:	DWG NO:			
				C-991-201-5128		
CHKD:			SCALE	SHEET	REV.	
DRAW:			N/A	1/1	A0	