





REV	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW VERSION	Colinye	Jerry	2023/12/07

Main Spec Specifications/主要技术参数

1. Material/材质:
Housing/塑胶: LCP, UL94 V-0; Natural(Beige)/本色(米黄色);
Pin/针脚: Phosphor bronze, Sn-Plated/磷青铜, 镀锡;
Tab/焊片: Brass, Sn-Plated/黄铜, 镀锡;
2. Rated Current/额定电流: 2.0A AC/DC;
3. Rated Voltage/额定电压: 100V AC/DC;
4. Contact Resistance/接触电阻: 20mΩ;
5. Insulation Resistance/绝缘阻抗: 500MΩ;
6. Withstand Voltage/耐电压: 500V AC/minute;
7. Temperature Range/工作温度: -40℃~+125℃
8. Poles/线数: 02 to 15 ;
9. Order information/编码原则: 991-XX1-7120

Poles/线数



PCB LAYOUT

NO	P/N	DIM(mm)			NO	P/N	DIM(mm)		
		A	B	C			A	B	C
1	991-021-7120	7.30	1.50	4.45	8	991-091-7120	17.80	12.00	14.95
2	991-031-7120	8.80	3.00	5.95	9	991-101-7120	19.30	13.50	16.45
3	991-041-7120	10.30	4.50	7.45	10	991-111-7120	20.80	15.00	17.95
4	991-051-7120	11.80	6.00	8.95	11	991-121-7120	22.30	16.50	19.45
5	991-061-7120	13.30	7.50	10.45	12	991-131-7120	23.80	18.00	20.95
6	991-071-7120	14.80	9.00	11.95	13	991-141-7120	25.30	19.50	22.45
7	991-081-7120	16.30	10.50	13.45	14	991-151-7120	26.80	21.00	23.95


X. ± 0.50 X. ° ± 5°
.X ± 0.30 .X ° ± 3°
.XX ± 0.20 .XX ° ± /
.XXX ± 0.10 .XXX ° ± /
UNITS: mm

The information in this document is property of JiDC company and should not be copied or reproduced in any other way, without written permission.



Guangdong JiDe Precision Electronics Co., Ltd
广东济德精密电子有限公司

TITLE: 1.50mm PITCH SIDE ENTRY TYPE CONNECTOR	PART NO. 991-XX1-7120
APPD:	DWG NO: C-991-XX1-7120
CHKD:	
DRAW:	



SCALE	SHEET	REV.
1:1	1/1	A0