




X. ± 0.50		X.° ± 1°	Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司			
.X ± 0.30		.X° ± 0.5°				
.XX ± 0.20		.XX° ± /	TITLE: 2.20mm Pitch 32PIN Male 90° DIP PART NO. 991-321-5128			
.XXX ± 0.15		.XXX° ± /				
UNITS:		mm	DWG NO: C-991-321-5128			
The information in this document is property of JiDC company and should not be copied or reproduced in any other way, without written permission.						
			APPD:		SCALE N/A	
			CHKD:			
DRAW:			REV. AO			

- Specifications:
- Contact Resistance/接触电阻: ≤20mΩ
 - Insulation Resistance/绝缘电阻: ≥100MΩ
 - Rated Voltage/额定电压: 50V Max AC/DC
 - Rated Current/额定电流: 3.0A Max AC/DC
 - Withstand Voltage/耐压: 1000v Ac/minute
 - Temperature Range/工作温度范围: -40℃~+125℃
 - Housing/外壳: PPS UL94V-0 Grey
 - Contacts/端子: Brass Sn-Plated
 - RoHS Compliance/产品符合RoHS;