






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
PM2.54-2Z01P-H85	2*1	0.00	2.54
PM2.54-2Z02P-H85	2*2	2.54	5.08
PM2.54-2Z03P-H85	2*3	5.08	7.62
PM2.54-2Z04P-H85	2*4	7.62	10.16
PM2.54-2Z05P-H85	2*5	10.16	12.70
PM2.54-2Z06P-H85	2*6	12.70	15.24
PM2.54-2Z07P-H85	2*7	15.24	17.78
PM2.54-2Z08P-H85	2*8	17.78	20.32
PM2.54-2Z09P-H85	2*9	20.32	22.86
.....			
PM2.54-2Z40P-H85	2*40	(40-1)X2.54	(40)X2.54

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	±0.30	X.*	±5°	PART NO.	TITLE: 2.54FH H8.5 2xnpin
.XX	±0.20	X.X*	±1°	PM2.54-2ZNP-H85	180度 Y型 PC3.2 6T
.XXX	±0.10	X.XX*	±0.5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---		SCALE	SHEET	
			N:A	1/1	