





REV.	REVISION DESCRIPTION	DATE	APPD
B.	材质PBT改为Nylon	23.6.19	Wu Hui

1 Pin:



- NOTES:
1. Rated voltage: 250V AC.DC
 2. Rated current: 7A AC DC
 3. Contact resistance: $\leq 10 \text{ m}\Omega$
 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 5. Withstand voltage: 1500V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : Nylon UL94V-0(2)
 8. Pin Materials : Brass / Tin-Plated.

2~6 Pin:





PCB LATOUT



Circuits	Type	Dimension mm	
		A	B
1	TJC1-1A	-	-
2	TJC1-2A	10.0	18.0
3	TJC1-3A	18.0	26.0
4	TJC1-4A	26.0	34.0
5	TJC1-5A	34.0	42.0
6	TJC1-6A	42.0	50.0

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: TJC1-A	TITLE: 10.0-8...8 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X°: ± 2.0°	DR: Chen Quan Long	DATE:21/08/01
.XXX: ± 0.01	.XX°: ± 1.0°	DATE:21/08/01	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD:Ren An De	PAGE: 1/1
		DATE:21/08/01	UNITS: mm
			REV.: B

1 Pin:



2-6 Pin:




NOTES:

1. Rated voltage: 250V AC/DC
2. Rated current: 7A AC/DC
3. Contact resistance: $\leq 10 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria

Circuits	Type	Dimension mm	
		A	B
1	TJC1-1Y	-	-
2	TJC1-2Y	10.0	16.0
3	TJC1-3Y	18.0	24.0
4	TJC1-4Y	26.0	32.0
5	TJC1-5Y	34.0	40.0
6	TJC1-6Y	42.0	48.0

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^\circ$	PRODUCT NAME: TJC1-Y		TITLE: 10.0-8...8 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	DR: Yuan Jun Rong	DATE: 2021/05/03	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^\circ$	CHKD: Wu Hui	DATE: 2021/05/03	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 2021/05/03	UNITS: mm	REV.: A
DRAWING NO:					



NOTES

Used in TJC1-Y Series Housing.
Accepts AWG #24~18 Wire Range.
0.2~ 0.75 mm² .
Insulation O.D.=0.5~3.2 mm.
Material : Phosphor Bronze .
Finish: Tin plated.
Qty/Reel: 5,000 PCS.
Thickness: 0.25 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: TJC1-T		TITLE: 10.0-8...8mm Pitch Wire To Board Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Yuan Jun Rong	DATE:20.3.31	SCALE: N/A	
FINISH:		CHKD:Wu Hui	DATE:20.3.31	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:20.3.31	UNITS: mm	REV.: A