







SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
PM2.54-1Z01P-H85	1	0.00	2.54
PM2.54-1Z02P-H85	2	2.54	5.08
PM2.54-1Z03P-H85	3	5.08	7.62
PM2.54-1Z04P-H85	4	7.62	10.16
PM2.54-1Z05P-H85	5	10.16	12.70
PM2.54-1Z06P-H85	6	12.70	15.24
PM2.54-1Z07P-H85	7	15.24	17.78
PM2.54-1Z08P-H85	8	17.78	20.32
PM2.54-1Z09P-H85	9	20.32	22.86
.....			
PM2.54-1Z40P-H85	40	(40-1)X2.54	(40)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. PM2.54-1ZNP-H85	TITLE: 2.54FH H8.5 1xnPin 180度 Y型 PC3.2 6T		
.XX ±0.20	X.X* ±1°				
.XXX ±0.10	X.XX*±0.5°				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1