



1. FIGURE AND DIMENSIONS (视图及尺寸)



孔位 排列						
(芯数)	2P (2)	3P (3)	4P (4)	5P (5)	6P (6)	7P (7)
额定 电流	额定电流: 5A	额定电流: 5A	额定电流: 5A	额定电流: 3A	额定电流: 3A	额定电流: 3A

版本			TITLE			DRAWING NO.		REV.
REVA4			PART NO.			FG. GX12. P04. CAL		A0
REVA3								
REVA2								
REVA1								
DRAW		DATE						
CHECK		DATE	USE			XKB INDUSTRIAL PRECISION CO., LIMITED		
APPR'D		DATE						

Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	1000
2. Working Temperature (温度)	-50~+70°
3. IP Rating (防护级别)	IP 50
5. Rated voltage (额定电压)	400V
6. Rated Current (额定电流)	5
7. Shell material (壳体材质)	Zinc alloy nickel plated/锌合金镀镍
8. Pin Material (插针材料)	Copper gilding (铜镀金)
9. Insulation resistance (绝缘电阻)	>100MΩ
10. Insulator material (绝缘体材料)	橡胶黑木
11. Salt spray test (盐雾测试)	>48H

Sum up (总结)	
Series (系列)	GX12
Shell style/model (外壳样式/型号)	GX12: Fixed socket, front and rear panel mount type/固定式插座, 前后面板安装型
Button (按键)	1 button (1个按键)
Termination type (终止类型)	Male solder (公板接)
Line diameter awg (线材直径)	-
Cable diameter Φ (电缆直径)	-
Match plug (匹配插头)	-