







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C
2	1.50	3.35	4.46
3	3.00	4.85	5.96
4	4.50	6.35	7.46
5	6.00	7.85	8.96
6	7.50	9.35	10.46
7	9.00	10.85	11.96
8	10.50	12.35	13.46
9	12.00	13.85	14.96
10	13.50	15.35	16.46
11	15.00	16.85	17.96
12	16.50	18.35	19.46
13	18.00	19.85	20.96
14	19.50	21.35	22.46
15	21.00	22.85	23.96





PIN 2~3



PIN 4~7

- 技术指标:
- 1.温度范围: -25℃~85℃
 - 2.额定电压: 350V, AC/DC
 - 3.接触电阻: ≤0.02Ω
 - 4.绝缘电阻: ≥1000MΩ
 - 5.额定电流: 3A,AC/DC



2	插针	铜	镀锡	
1	基座	PA6T	米色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	品 名 TITLE		针座	
X. ±0.50 .XX ±0.10		单 位 UNIT	MM	料 号 PART NO		HC-ZE1.5-5PLT	
.X ±0.20 .XXX ±0.05		张 数 PART NO	1 OF 1	制 图 DRAW	AhYe		
ANGLES ±1°		版 本 REV	A	审 核 CHECKED	夏操云		
				批 准 APPROVE	赵亮亮		