






标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

PCB LAYOUT

| Pin | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2   | 7.50  | 6.10  | 2.50  |
| 3   | 10.00 | 8.60  | 5.00  |
| 4   | 12.50 | 11.10 | 7.50  |
| 5   | 15.00 | 13.60 | 10.00 |
| 6   | 17.50 | 16.10 | 12.50 |
| 7   | 20.00 | 18.60 | 15.00 |
| 8   | 22.50 | 21.10 | 17.50 |
| 9   | 25.00 | 23.60 | 20.00 |
| 10  | 27.50 | 26.10 | 22.50 |
| 11  | 30.00 | 28.60 | 25.00 |
| 12  | 32.50 | 31.10 | 27.50 |
| 13  | 35.00 | 33.60 | 30.00 |
| 14  | 37.50 | 36.10 | 32.50 |
| 15  | 40.00 | 38.60 | 35.00 |

技术要求:

适应基板厚度: 1.2mm~1.6mm

温度范围: -25°C~85°C

额定电压: 250V AC/DC

额定电流: 3A

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V AC/minute

|     |     |      |       |     |
|-----|-----|------|-------|-----|
| 2   | 插针  | 铜    | 镀锡    |     |
| 1   | 底座  | PA66 | 白色    |     |
| 序 号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

|                |               |
|----------------|---------------|
| 品 名<br>TITLE   | 针座            |
| 料 号<br>PART NO | HC-XHB-7AW-TW |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 列  
SCALE

1:1

X.X ±0.35 X' ±3.00'

单 位  
UNIT

MM

X.XX ±0.25 X.X' ±2.00'

张 数  
PART NO

1 OF 1

X.XXX ±0.15 X.XX' ±1.00'

版 本  
REV

A

制 图  
DRAW审 核  
CHECKED批 准  
APPROVE

AhYe

夏操云

赵亮亮

