





Pin	DIM A	DIM B
2	7.50	2.60
3	10.00	2.60
4	12.50	3.60
5	15.00	6.30
6	17.50	8.80
7	20.00	11.30
8	22.50	13.80
9	25.00	16.30
10	27.50	18.80
11	30.00	21.30
12	32.50	23.80
13	35.00	26.30
14	37.50	28.80
15	40.00	31.30
16	42.50	33.80



耐 压: 1000V AC/minute

	深圳市虹成电子有限公司		品 名 TITLE		针座	
			料 号 PART NO		HC-XHB-9A-TW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1 : 1			
X.X ±0.35	X' ±3.00'	单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX ±0.25	X.X' ±2.00'	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
X.XXX ±0.15	X.XX' ±1.00'	版 本 REV	A	批 准 APPROVE	赵亮亮	