



| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |


A



B




C




D

E



F

G



| CKI | DIM A | DIM B |
|-----|-------|-------|
| 2   | 2.00  | 6.0   |
| 3   | 4.00  | 8.0   |
| 4   | 6.00  | 10.00 |
| 5   | 8.00  | 12.00 |
| 6   | 10.00 | 14.00 |
| 7   | 12.00 | 16.00 |
| 8   | 14.00 | 18.00 |
| 9   | 16.00 | 20.00 |
| 10  | 18.00 | 22.00 |
| 11  | 20.00 | 24.00 |
| 12  | 22.00 | 26.00 |
| 13  | 24.00 | 28.00 |
| 14  | 26.00 | 30.00 |
| 15  | 28.00 | 32.00 |
| 16  | 30.00 | 34.00 |
| 17  | 32.00 | 36.00 |
| 18  | 34.00 | 38.00 |
| 19  | 36.00 | 40.00 |
| 20  | 38.00 | 42.00 |

A

B

C

D

E

F

G

技术指标:

- 1.工作温度:  $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
- 2.额定电压: 250V, DC/AC(rms)
- 3.额定电流: 3.0A AC,DC
- 4.接触电阻:  $\leq 20\text{m}\Omega$
- 5.耐 压: 800V AC/minute
- 6.绝缘电阻:  $\geq 1000\text{M}\Omega$

| 2   | 插针  | 铜    | 镀锡    |     |
|-----|-----|------|-------|-----|
| 1   | 基座  | PA66 | 米色    |     |
| 序 号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

| 品 名<br>TITLE   | 针座              |
|----------------|-----------------|
| 料 号<br>PART NO | HC-PHD2.0-2x4AW |

| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) | 比 列<br>SCALE   | 1:1    | 制 图<br>DRAW    | AhYe |  |
|------------------------------------------|----------------|--------|----------------|------|--|
| X. $\pm 0.50$ .XX $\pm 0.10$             | 单 位<br>UNIT    | MM     | 审 核<br>CHECKED | 夏操云  |  |
| .X $\pm 0.20$ .XXX $\pm 0.05$            | 张 数<br>PART NO | 1 OF 1 | 批 准<br>APPROVE | 赵亮亮  |  |
| ANGLES $\pm 1^{\circ}$                   | 版 本<br>REV     | A      |                |      |  |