







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Pin Number	Signal Name	Pin Number	Signal Name
1	VBUS	5	SSRX-
2	D-	6	SSRX+
3	D+	7	GND
4	GND	8	SSTX-
Shell	Shield	9	SSTX+




7.25±0.15




SPECIFICATIONS:
Contact current Rating:
1.8 Amperes for pin1&pin4.
0.25 Amperes other contacts
Dielectric Withstanding Voltage: AC 100V(RMS)
Insulation resistance:100Megohms Minimum.
Contact Resistance:
30m Ω Max for pin1&pin4
50m Ω Max for other contacts
Mechanical Characteristics:
Mating Force: 35 Newtoms.Maximum
Unmating Force:10 Newtoms.Minimum.
8N Min After Durability

MATERIAL:
Housing: PBT Blue
Contact: copper alloy(T=0.2mm)
Shell: SUS304
PLATING:
Contact: Au Plated on contact area
Tin Plated on solder area
Nickel underplating over all
Shell: Nickel Plated
operating Temperature: -55*to+85°



PCB EDGE



3	外壳	不锈钢	镀镍	
2	接触	铜	镀金	
1	基座	PBT	蓝色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	USB座
料 号 PART NO	HC-USB3.0-L257-J

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	制 图 DRAW		审 核 CHECKED		批 准 APPROVE	
X. +/-	METRIC 0.35	单 位 UNIT	MM	制 图 DRAW	AhYe				
.X +/-	0.35	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云				
.XX +/-	0.25	版 本 REV	A	批 准 APPROVE	赵亮亮				
FRACTIONS +/-									
ANGLES +/-	2.00°								