





Pin	DIM A	DIM B
2	7.50	2.60
3	10.00	2.60
4	12.50	3.60
5	15.00	6.30
6	17.50	8.80
7	20.00	11.30
8	22.50	13.80
9	25.00	16.30
10	27.50	18.80
11	30.00	21.30
12	32.50	23.80
13	35.00	26.30
14	37.50	28.80
15	40.00	31.30
16	42.50	33.80



适应基板厚度：1.2mm~1.6mm
温度范围：-25℃~85℃
额定电压：250V AC/DC
额定电流：3A
接触电阻： $\leq 0.01\Omega$
绝缘电阻： $\geq 1000M\Omega$
耐 压：1000V AC/minute

成电子有限公司	品 名 TITLE	针座
	料 号 PART NO	HC-XHB-8A-TW

