

| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |

| Pin | DIM A | DIM B |
|-----|-------|-------|
| 2   | 7.50  | 0.00  |
| 3   | 10.00 | 2.50  |
| 4   | 12.50 | 5.00  |
| 5   | 15.00 | 7.50  |
| 6   | 17.50 | 10.00 |
| 7   | 20.00 | 12.50 |
| 8   | 22.50 | 15.00 |
| 9   | 25.00 | 17.50 |
| 10  | 27.50 | 20.00 |
| 11  | 30.00 | 22.50 |
| 12  | 32.50 | 25.00 |
| 13  | 35.00 | 27.50 |
| 14  | 37.50 | 30.00 |
| 15  | 40.00 | 32.50 |

A

B

C

D

E

F

G

A

B



C

D




E

F

G



2PIN




PCB LAYOUT

技术要求:

适应基板厚度: 1.2mm~1.6mm  
温度范围: -25℃~85℃  
额定电压: 250V AC/DC  
额定电流: 3A  
接触电阻: ≤0.01Ω  
绝缘电阻: ≥1000MΩ  
耐 压: 1000V AC/minute

|    |     |      |       |     |
|----|-----|------|-------|-----|
| 2  | 插针  | 铜    | 镀锡    |     |
| 1  | 基座  | PA66 | 白色    |     |
| 序号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |

|                                                                                                   |              |                |              |                                                                                       |
|---------------------------------------------------------------------------------------------------|--------------|----------------|--------------|---------------------------------------------------------------------------------------|
|  深圳市虹成电子有限公司 |              | 品 名<br>TITLE   | 针座           |                                                                                       |
|                                                                                                   |              | 料 号<br>PART NO | HC-XH-6AW-TW |                                                                                       |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                          |              | 比 列<br>SCALE   | 1:1          |  |
| X.X ±0.35                                                                                         | X* ±3.00*    | 单 位<br>UNIT    | MM           | 制 图<br>DRAW                                                                           |
| X.XX ±0.25                                                                                        | X.X* ±2.00*  | 张 数<br>PART NO | 1 OF 1       | 审 核<br>CHECKED                                                                        |
| X.XXX ±0.15                                                                                       | X.XX* ±1.00* | 版 本<br>REV     | A            | 批 准<br>APPROVE                                                                        |
|                                                                                                   |              | 制 图<br>DRAW    | AhYe         |  |
|                                                                                                   |              | 审 核<br>CHECKED | 夏操云          |                                                                                       |
|                                                                                                   |              | 批 准<br>APPROVE | 赵亮亮          |                                                                                       |