

标 记
MARK

ECN编号/变更内容
ECN NO/DEFINITION

修 改
REVISE

日 期
DATE

核 准
APPROVE

A

B

C

D

E

F

G

A

B








C

D

E

F

G



PCB板开孔建议

SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触抗阻): $30\text{m}\Omega$
5. Insulation Resistance(绝缘抗阻): $100\text{M}\Omega$
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.

3	IEC母头	冷扎板	镀镍	
2	支架	冷扎板	镀铜锡	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	屏蔽罩
料 号 PART NO	HC-PBZ-I047R

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



0-10: ± 0.20 26-50: ± 0.40
11-25: ± 0.30 ANGULAR: $\pm 2^{\circ}$

单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮

