

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

A

B

C

D

E

F

G

A

B







C

D

E

F

G



CKI	DIM A	DIM B
2	1.50	6.00
3	3.00	7.50
4	4.50	9.00
5	6.00	10.50
6	7.50	12.00
7	9.00	13.50
8	10.50	15.00
9	12.00	16.50
10	13.50	18.00
11	15.00	19.50
12	16.50	21.00
13	18.00	22.50
14	19.50	24.00
15	21.00	25.50
16	22.50	27.00
17	24.00	28.50
18	25.50	30.00
19	27.00	31.50
20	28.50	33.00

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
2. 额定电压: 100V, AC/DC
3. 接触电阻: $\leq 0.02\Omega$
4. 绝缘电阻: $\geq 500\text{M}\Omega$
5. 额定电流: 1A, AC/DC

2	插针	铜	镀锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HCZZ0068-10

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1	制 图 DRAW	AhYe	审 核 CHECKED	夏操云	批 准 APPROVE	赵亮亮
X. ± 0.50	. XX ± 0.10	单 位 UNIT	MM					
. X ± 0.20	. XXX ± 0.05	张 数 PART NO	1 OF 1					
ANGLES $\pm 1^{\circ}$		版 本 REV	A					

