





SPECIFICATION (技术要求)

- 1. Operating Temperature(环境温度): -25℃~85℃
- 2. Voltage Rating(额定电压): 50V AC/DC
- 3. Current Rating(额定电流): 0.5A
- 4. Contact Resistance(接触抗阻): 30mΩ
- 5. Insulation Resistance(绝缘抗阻): 100MΩ
- 6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
- 7. Insertion/Withdrawal Force(插拔力): 3-50N
- 8. Life Time(mating cycles)寿命: >1000 Cycles
- 9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
- 10. NOMINAL IMPEDANCE : 75 OHMS.
- 11. OPERATING FREQUENCY : 0-2 GHZ.

3	IEC母头	冷扎板	镀镍	
2	支架	SPCC	镀铜锡	
1	绝缘体	PPS	黑色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	屏蔽罩	
			料号 PART NO	HC-PBZ-I033L	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1		
0-10: ±0.3 26-50: ±0.5		单位 UNIT	MM	制图 DRAW	AhYe
11-25: ±0.4 ANGULAR: ±2°		张数 PART NO	1 OF 1	审核 CHECKED	夏操云
		版本 REV	A	批准 APPROVE	赵亮亮

