






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Pin	DIM A	DIM B	DIM C
2	7.50	6.10	2.50
3	10.00	8.60	5.00
4	12.50	11.10	7.50
5	15.00	13.60	10.00
6	17.50	16.10	12.50
7	20.00	18.60	15.00
8	22.50	21.10	17.50
9	25.00	23.60	20.00
10	27.50	26.10	22.50
11	30.00	28.60	25.00
12	32.50	31.10	27.50
13	35.00	33.60	30.00
14	37.50	36.10	32.50
15	40.00	38.60	35.00



PCB LAYOUT

技术要求:

适应基板厚度: 1.6mm
温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 3A
接触电阻: ≤0.02Ω
绝缘电阻: ≥1000MΩ
耐 压: 1000V AC/minute

2	插针	铜	镀锡	
1	底座	PA66	白色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HC-XHB-6A-TW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.X ±0.35	X' ±3.00'	单 位 UNIT	MM	制 图 DRAW	AhYe
X.XX ±0.25	X.X' ±2.00'	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
X.XXX ±0.15	X.XX' ±1.00'	版 本 REV	A	批 准 APPROVE	赵亮亮

