

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C
2	2.00	6.0	3.2
3	4.00	8.0	3.2
4	6.00	10.00	3.0
5	8.00	12.00	5.0
6	10.00	14.00	7.0
7	12.00	16.00	9.0
8	14.00	18.00	11.00
9	16.00	20.00	13.00
10	18.00	22.00	15.00
11	20.00	24.00	17.00
12	22.00	26.00	19.00
13	24.00	28.00	21.00
14	26.00	30.00	23.00
15	28.00	32.00	25.00
16	30.00	34.00	27.00
17	32.00	36.00	29.00
18	34.00	38.00	31.00
19	36.00	40.00	33.00
20	38.00	42.00	35.00

A

B

C

D

E

F

G

A

B





C

D



E

F

G



- 技术指标:
- 1.工作温度: -25℃~85℃
 - 2.额定电压: 250V, DC/AC(rms)
 - 3.耐 压 值: 800V AC/minute
 - 4.接触电阻: ≤20mΩ
 - 5.绝缘电阻: ≥1000MΩ
 - 6.额定电流: 3.0A AC,DC



2	插针	铜	镀锡	
1	基座	PA46	米色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-PHB2. 0-2x3A

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1	制 图 DRAW		AhYe	审 核 CHECKED	夏操云	批 准 APPROVE	赵亮亮
X. ±0.50 .XX ±0.10	单 位 UNIT	MM							
.X ±0.20 .XXX ±0.05	张 数 PART NO	1 OF 1							
ANGLES ±1°	版 本 REV	A							

