

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C
2	2.00	4.90	8.00
3	4.00	6.90	10.00
4	6.00	8.90	12.00
5	8.00	10.90	14.00
6	10.00	12.90	16.00
7	12.00	14.90	18.00
8	14.00	16.90	20.00
9	16.00	18.90	22.00
10	18.00	20.90	24.00
11	20.00	22.90	26.00
12	22.00	24.90	28.00
13	24.00	26.90	30.00
14	26.00	28.90	32.00
15	28.00	30.90	34.00
16	30.00	32.90	36.00

A

B

C

D

E

F

G

A

B








C

D


E

F


G



2P 结构样式



3P 结构样式



适用线路板(PCB LAYOUT)

技术指标:

1. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$
2. 额定电压: 200V, AC
3. 接触电阻: $\leq 55\text{m}\Omega$ (Initial) per contact
 $\leq 25\text{m}\Omega$ Change allowed
4. 绝缘电阻: $\geq 1000\text{M}\Omega$

2	插针	铜	镀锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HCZZ0398-14

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	制 图 DRAW		AhYe
X. ± 0.50	.XX ± 0.10	单 位 UNIT	MM	张 数 PART NO	1 OF 1	审 核 CHECKED
.X ± 0.20	.XXX ± 0.05	版 本 REV	A	批 准 APPROVE	夏操云	赵亮亮
ANGLES $\pm 1^{\circ}$						

