




Pin	DIM A	DIM B
2	3.96	7.92
3	7.92	11.88
4	11.88	15.84
5	15.84	19.80
6	19.80	23.76
7	23.76	27.72
8	27.72	31.68
9	31.68	35.64
10	35.64	39.60
11	39.60	43.56
12	43.56	47.52



耐 压: 1500V AC/minute



	深圳市虹成电子有限公司			品 名	针座	
				TITLE		
				料 号	HCZZ0324-8	
				PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1 : 1			
X.X ±0.35	X'. ±3.00'	单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX ±0.25	X.X' ±2.00'	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
X.XXX ±0.15	X.XX' ±1.00'	版 本 REV	A	批 准 APPROVE	赵亮亮	