






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE




SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): -25℃~85℃
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触抗阻): 30mΩ
5. Insulation Resistance(绝缘抗阻): 100MΩ
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
10. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
11. NOMINAL IMPEDANCE : 75 OHMS.
12. OPERATING FREQUENCY : 0-2 GHZ.



PCB LAYOUT
(TOP VIEW)
P. C. B开孔示意图

3	IEC母头	冷扎板	镀镍	
2	支架	SPCC	镀镍	
1	绝缘体	PPS	黑色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	屏蔽罩	
		料 号 PART NO	HC-PBZ-I70	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
0-10: ±0.2 26-50: ±0.4		单 位 UNIT	MM	制 图 DRAW
11-25: ±0.3 ANGULAR: ±2°		张 数 PART NO	1 OF 1	审 核 CHECKED
		版 本 REV	A	批 准 APPROVE
				夏操云
				赵亮亮

