






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C
2	1.50	3.35	4.46
3	3.00	4.85	5.96
4	4.50	6.35	7.46
5	6.00	7.85	8.96
6	7.50	9.35	10.46
7	9.00	10.85	11.96
8	10.50	12.35	13.46
9	12.00	13.85	14.96
10	13.50	15.35	16.46
11	15.00	16.85	17.96
12	16.50	18.35	19.46
13	18.00	19.85	20.96
14	19.50	21.35	22.46
15	21.00	22.85	23.96





PIN 2~3



PIN 4~7

技术指标:

- 1.温度范围: -25℃~85℃
- 2.额定电压: 350V, AC/DC
- 3.接触电阻: ≤0.02Ω
- 4.绝缘电阻: ≥1000MΩ
- 5.额定电流: 3A, AC/DC



2	插针	铜	镀锡	
1	基座	PA6T	米白色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-ZE1.5-4PWT

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1	制 图 DRAW		AhYe
X. ±0.50 .XX ±0.10	单 位 UNIT	MM	张 数 PART NO	1 OF 1	审 核 CHECKED
.X ±0.20 .XXX ±0.05	版 本 REV	A	批 准 APPROVE	夏操云	赵亮亮
ANGLES ±1°					

