

标 记  
MARK

ECN编号/变更内容  
ECN NO/DEFINITION

修 改  
REVISE

日 期  
DATE

核 准  
APPROVE

A

B

C

D

E

F

G

A

B



C

D

E


F

G




SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): -25℃~85℃
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触抗阻): 30mΩ
5. Insulation Resistance(绝缘抗阻): 100MΩ
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.



P. C. B 参考图



|    |     |     |       |     |
|----|-----|-----|-------|-----|
| 3  | F头  | 锌合金 | 镀镍    |     |
| 2  | 支架  | 马口铁 | — —   |     |
| 1  | 绝缘体 | PPS | 棕色    |     |
| 序号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

|                |              |
|----------------|--------------|
| 品 名<br>TITLE   | 屏蔽罩          |
| 料 号<br>PART NO | HC-PBZ-R2414 |

|                                                       |                |        |                |      |
|-------------------------------------------------------|----------------|--------|----------------|------|
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)              | 比 列<br>SCALE   | 1:1    |                |      |
| 0-10: ±0.20 26-50: ±0.40<br>11-25: ±0.30 ANGULAR: ±2° | 单 位<br>UNIT    | MM     | 制 图<br>DRAW    | AhYe |
|                                                       | 张 数<br>PART NO | 1 OF 1 | 审 核<br>CHECKED | 夏操云  |
|                                                       | 版 本<br>REV     | A      | 批 准<br>APPROVE | 赵亮亮  |

