



Pin	DIM A	DIM B	DIM C
2	4.50	1.50	3.60
3	6.00	3.00	5.10
4	7.50	4.50	6.60
5	9.00	6.00	8.10
6	10.50	7.50	9.60
7	12.00	9.00	11.10
8	13.50	10.50	12.60
9	15.00	12.00	14.10
10	16.50	13.50	15.60
11	18.00	15.00	17.10
12	19.50	16.50	18.60
13	21.00	18.00	20.10
14	22.50	19.50	21.60
15	24.00	21.00	23.10
16	25.50	22.50	24.60



耐 压: 800V AC/minute

		深圳市虹成电子有限公司		品 名 TITLE		针座	
				料 号 PART NO		HCZZ0445-11	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE		1 : 1			
X.X ±0.35 X'. ±3.00'		单 位 UNIT		MM		制 图 DRAW	
X.XX ±0.25 X.X' ±2.00'		张 数 PART NO		1 OF 1		审 核 CHECKED	
X.XXX ±0.15 X.XX' ±1.00'		版 本 REV		A		批 准 APPROVE	
						AhYe	
						夏操云	
						赵亮亮	
							