

标 记
MARK

ECN编号/变更内容
ECN NO/DEFINITION

修 改
REVISE

日 期
DATE

核 准
APPROVE

A

B

C

D

E

F

G

A

B



C

D

E



F

G




SPECIFICATION (技术要求)

1. Operating Temperature (环境温度): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
2. Voltage Rating (额定电压): 50V AC/DC
3. Current Rating (额定电流): 0.5A
4. Contact Resistance (接触抗阻): $30\text{m}\Omega$
5. Insulation Resistance (绝缘抗阻): $100\text{M}\Omega$
6. Dielectric Withstanding Voltage (耐电压): 500V AC Min
7. Insertion/Withdrawal Force (插拔力): 3-50N
8. Life Time (mating cycles) 寿命: >1000 Cycles
9. SIGNAL LOSS $<1\text{dB}$ IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.



PCB LAYOUT
(TOP VIEW)
P. C. B开孔示意图

3	F头	锌合金	镀镍	
2	支架	冷扎板	镀铜锡	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	屏蔽罩	
			料 号 PART NO	HC-PBZ-R032	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
0-10: ± 0.2 26-50: ± 0.4		单 位 UNIT	MM	制 图 DRAW	AhYe
11-25: ± 0.3 ANGULAR: $\pm 2^{\circ}$		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

