

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

PIN 数	A±0.2	B±0.2	C±0.2
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25
7P	13.85	10.75	7.50
8P	15.10	12.00	8.75
9P	16.35	13.25	10.00

A

B

C

D

E

F

G

A

B








C

D

E

F

G



Specifications:
Rated Voltage : 125V AC/DC
Rated Current : 1A AC,DC
Withstand Voltage : 200V AC/minute
Contact Resistance : 50mΩ(MAX.)
Insulation Resistance : 100MΩ(MIN.)
Storage Temperature Range: -40°C~+85°C;
Operation Temperature Range: -25°C~+70°C;

2	插针	铜	镀镍锡	
1	基座	LCP	本色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HCZZ0015-9	
UNLESS OTHERWISE, GENERAL TOLERANCE:		比 列 SCALE	1:1		
X. xxx ±0.05 X. xx ±0.15 X. x ±0.25		单 位 UNIT	MM	制 图 DRAW	AhYe
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

