

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C
4	3.00	4.55	6.30
5	4.00	5.55	7.30
6	5.00	6.55	8.30
7	6.00	7.55	9.30
8	7.00	8.55	10.30
9	8.00	9.55	11.30
10	9.00	10.55	12.30
11	10.00	11.55	13.30
12	11.00	12.55	14.30
13	12.00	13.55	15.30
14	13.00	14.55	16.30
15	14.00	15.55	17.30
16	15.00	16.55	18.30
17	16.00	17.55	19.30
18	17.00	18.55	20.30
19	18.00	19.55	21.30
20	19.00	20.55	22.30

A

B

C

D

E

F

G

A

B






C

D

E



F

G



技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
2. 额定电压: 50V, AC DC
3. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact
 $\leq 40\text{m}\Omega$ Change allowed
4. 绝缘电阻: $\geq 100\text{M}\Omega$
5. 额定电流: 1.0A AC DC



2	插针	铜	镀锡	
1	基座	PA6T	米色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-SHD1.0-2x6PLT

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X. ± 0.50	.XX ± 0.10	单 位 UNIT	MM	制 图 DRAW	AhYe	
.X ± 0.20	.XXX ± 0.05	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
ANGLES $\pm 1^{\circ}$		版 本 REV	A	批 准 APPROVE	赵亮亮	