





SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): -25℃~85℃
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触抗阻): 30mΩ
5. Insulation Resistance(绝缘抗阻): 100MΩ
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
10. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
11. NOMINAL IMPEDANCE : 75 OHMS.
12. OPERATING FREQUENCY : 0-2 GHZ.

3	IEC母头	冷扎钢	镀镍	
2	支架	SPCC	镀铜锡	
1	绝缘体	PPS	棕色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司			品名 TITLE	屏蔽罩	
			料号 PART NO	HC-PBZ-I047B	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
0-10: ±0.20 26-50: ±0.40		单位 UNIT	MM	制图 DRAW	AhYe
11-25: ±0.30 ANGULAR: ±2°		张数 PART NO	1 OF 1	审核 CHECKED	夏操云
		版本 REV	A	批准 APPROVE	赵亮亮

