







标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE




Recommend PCB Layout
Tolerance: ±0.05mm

SPECIFICATION (技术要求)

1. Operating Temperature (环境温度): -25℃~85℃
2. Voltage Rating (额定电压): 50V AC/DC
3. Current Rating (额定电流): 0.5A
4. Contact Resistance (接触抗阻): 30mΩ
5. Insulation Resistance (绝缘抗阻): 100MΩ
6. Dielectric Withstanding Voltage (耐电压): 500V AC Min
7. Insertion/Withdrawal Force (插拔力): 3-50N
8. Life Time (mating cycles) 寿命: >1000 Cycles
10. SIGNAL LOSS < 1dB IN BOTH VHF, UHF BAND.
11. NOMINAL IMPEDANCE : 75 OHMS.
12. OPERATING FREQUENCY : 0-2 GHZ.

3	F头	锌合金	镀镍	
2	支架	马口铁	CnSn	
1	绝缘体	PA66	棕色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	屏蔽罩	
		料 号 PART NO	HC-PBZ-R03550	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
.XX±0.20	X±0.40	单 位 UNIT	MM	制 图 DRAW AhYe
.X±0.30	ANGULAR: ±2°	张 数 PART NO	1 OF 1	审 核 CHECKED 夏操云
		版 本 REV	A	批 准 APPROVE 赵亮亮

