

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号

尺寸 (mm)

A

B

2X1AW

5.40

2X2AW

4.20

9.60

2X3AW

8.40

13.80

2X4AW

12.60

18.00

2X5AW

16.80

22.20

2X6AW

21.00

26.40

2X7AW

25.20

30.60

2X8AW

29.40

34.80

2X9AW

33.60

39.00

2X10AW

37.80

43.20

2X11AW

42.00

47.40

2X12AW

46.20

51.60

SPECIFICATIONS

- 1.Current Rating:7A AC, DC
2.Voltage Rating:600V AC, DC
3.Temperatuer Range: -25°C~+85°C
4.Contact Resistance: 20mΩ Max
5.Insulation Resistance: 1000MΩ Min
6.Withstanding Voltang: 1500V AC/minute
7.Material: Wafer Nylon66
PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	尼龙66	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名

TITLE

料 号

PART NO


针座

HC-5557-4.2-2x2AW

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



X.±0.25 X'±2'

.X±0.20 .X'±1'

.XX±0.15 .XX'±0.5'

.XXX±0.10 .XXX'±0.5'

单 位

UNIT

张 数

PART NO

版 本

REV

MM

1 OF 1

A

制 图

DRAW

审 核

CHECKED





批 准

APPROVE

AhYe

夏操云

赵亮亮



PCB LAYOUT