





标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

Pin	DIM A	DIM B	DIM C
2	7.92	11.88	8.96
3	15.84	19.80	16.88
4	23.76	27.72	24.80
5	31.68	35.64	32.72



技术要求:

适用基板厚度: 1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC


额定电流: 7A AC/DC

接触电阻: ≤0.02Ω

绝缘电阻: ≥1000MΩ

耐 压: 1500V AC/minute

2	插针	铜	镀锡	
1	基座	PA66	米色	
序 号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE	针 座	
		料 号 PART NO	HC-VH7.92-2A-TM	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	
X.X ±0.35 X* ±3.00*		单 位 UNIT	MM	制 图 DRAW AhYe
X.XX ±0.25 X.X* ±2.00*		张 数 PART NO	1 OF 1	审 核 CHECKED 夏操云
X.XXX ±0.15 X.XX* ±1.00*		版 本 REV	A	批 准 APPROVE 赵亮亮

