







标 记
MARK

ECN编号/变更内容
ECN NO/DEFINITION


修 改
REVISE

日 期
DATE

核 准
APPROVE



P. C. B 参考图



SPECIFICATION (技术要求)

1. Operating Temperature (环境温度): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
2. Voltage Rating (额定电压): 50V AC/DC
3. Current Rating (额定电流): 0.5A
4. Contact Resistance (接触抗阻): $30\text{m}\Omega$
5. Insulation Resistance (绝缘抗阻): $100\text{M}\Omega$
6. Dielectric Withstanding Voltage (耐压): 500V AC Min
7. Insertion/Withdrawal Force (插拔力): 3-50N
8. Life Time (mating cycles) 寿命: >1000 Cycles
9. SIGNAL LOSS $<1\text{dB}$ IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.

3	IEC母头	冷扎板	D. Ni	
2	支架	马口铁	— —	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	屏蔽罩
料 号 PART NO	HC-PBZ-I2030

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1		
0-10: ± 0.20 26-50: ± 0.40	单 位 UNIT	MM	制 图 DRAW	AhYe
11-25: ± 0.30 ANGULAR: $\pm 2^{\circ}$	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
	版 本 REV	A	批 准 APPROVE	赵亮亮

