






标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

PCB LAYOUT

| Pin | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2   | 7.50  | 6.10  | 2.50  |
| 3   | 10.00 | 8.60  | 5.00  |
| 4   | 12.50 | 11.10 | 7.50  |
| 5   | 15.00 | 13.60 | 10.00 |
| 6   | 17.50 | 16.10 | 12.50 |
| 7   | 20.00 | 18.60 | 15.00 |
| 8   | 22.50 | 21.10 | 17.50 |
| 9   | 25.00 | 23.60 | 20.00 |
| 10  | 27.50 | 26.10 | 22.50 |
| 11  | 30.00 | 28.60 | 25.00 |
| 12  | 32.50 | 31.10 | 27.50 |
| 13  | 35.00 | 33.60 | 30.00 |
| 14  | 37.50 | 36.10 | 32.50 |
| 15  | 40.00 | 38.60 | 35.00 |

技术要求:

适应基板厚度: 1.2mm~1.6mm

温度范围: -25°C~85°C

额定电压: 250V AC/DC


额定电流: 3A

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V AC/minute

|    |     |      |       |     |
|----|-----|------|-------|-----|
| 2  | 插针  | 铜    | 镀锡    |     |
| 1  | 底座  | PA66 | 白色    |     |
| 序号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |

|                                                                                       |              |                |                |                                                                                       |      |
|---------------------------------------------------------------------------------------|--------------|----------------|----------------|---------------------------------------------------------------------------------------|------|
|  | 深圳市虹成电子有限公司  |                | 品 名<br>TITLE   | 针座                                                                                    |      |
|                                                                                       |              |                | 料 号<br>PART NO | HC-XHB-8AW-TW                                                                         |      |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                              |              | 比 列<br>SCALE   | 1:1            |  |      |
| X.X ±0.35                                                                             | X' ±3.00'    | 单 位<br>UNIT    | MM             | 制 图<br>DRAW                                                                           | AhYe |
| X.XX ±0.25                                                                            | X.X' ±2.00'  | 张 数<br>PART NO | 1 OF 1         | 审 核<br>CHECKED                                                                        | 夏操云  |
| X.XXX ±0.15                                                                           | X.XX' ±1.00' | 版 本<br>REV     | A              | 批 准<br>APPROVE                                                                        | 赵亮亮  |

