





标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修改 REVISE	日期 DATE	核准 APPROVE

- SPECIFICATION (技术要求)
- 1. Operating Temperature(环境温度): -25℃~85℃
 - 2. Voltage Rating(额定电压): 50V AC/DC
 - 3. Current Rating(额定电流): 0.5A
 - 4. Contact Resistance(接触抗阻): 30mΩ
 - 5. Insulation Resistance(绝缘抗阻): 100MΩ
 - 6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
 - 7. Insertion/Withdrawal Force(插拔力): 3-50N
 - 8. Life Time(mating cycles)寿命: >1000 Cycles
 - 9. SIGNAL LOSS<1dB IN BOTH VHF, UHF BAND.
 - 10. NOMINAL IMPEDANCE : 75 OHMS.
 - 11. OPERATING FREQUENCY : 0-2 GHZ.

3	IEC母头	冷扎板	镀镍	
2	支架	马口铁	— —	
1	绝缘体	PPS	黑色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品名 TITLE		屏蔽罩	
		料号 PART NO		HC-PBZ-I2414MFB	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比例 SCALE	1:1		
0-10: ±0.20 26-50: ±0.40		单位 UNIT	MM	制图 DRAW	AhYe
11-25: ±0.30 ANGULAR: ±2°		张数 PART NO	1 OF 1	审核 CHECKED	夏操云
		版本 REV	A	批准 APPROVE	赵亮亮



P. C. B 参考图