



标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE


A



B




C




D

E



F

G



CKI	DIM A	DIM B
2	2.00	6.0
3	4.00	8.0
4	6.00	10.00
5	8.00	12.00
6	10.00	14.00
7	12.00	16.00
8	14.00	18.00
9	16.00	20.00
10	18.00	22.00
11	20.00	24.00
12	22.00	26.00
13	24.00	28.00
14	26.00	30.00
15	28.00	32.00
16	30.00	34.00
17	32.00	36.00
18	34.00	38.00
19	36.00	40.00
20	38.00	42.00

技术指标:

- 1.工作温度: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
- 2.额定电压: 250V, DC/AC(rms)
- 3.额定电流: 3.0A AC,DC
- 4.接触电阻: $\leq 20\text{m}\Omega$
- 5.耐 压: 800V AC/minute
- 6.绝缘电阻: $\geq 1000\text{M}\Omega$

2	插针	铜	镀锡	
1	基座	PA66	米色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	品 名 TITLE		针 座	
X. ± 0.50 .XX ± 0.10		单 位 UNIT	MM	料 号 PART NO		HC-PHD2.0-2x2AW	
.X ± 0.20 .XXX ± 0.05		张 数 PART NO	1 OF 1	制 图 DRAW	AhYe		
ANGLES $\pm 1^{\circ}$		版 本 REV	A	审 核 CHECKED	夏操云		
				批 准 APPROVE	赵亮亮		