





标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编 号	尺寸 (mm)	
	A	B
2X1AW		5.40
2X2AW	4.20	9.60
2X3AW	8.40	13.80
2X4AW	12.60	18.00
2X5AW	16.80	22.20
2X6AW	21.00	26.40
2X7AW	25.20	30.60
2X8AW	29.40	34.80
2X9AW	33.60	39.00
2X10AW	37.80	43.20
2X11AW	42.00	47.40
2X12AW	46.20	51.60

SPECIFICATIONS
1.Current Rating:7A AC, DC
2.Voltage Rating:600V AC, DC
3.Temperatuer Range: -25°C~+85°C
4.Contact Resistance: 20mΩ Max
5.Insulation Resistance: 1000MΩ Min
6.Withstanding Voltang: 1500V AC/minute
7.Material: Wafer Nylon66
PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	尼龙66	本色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HC-5557-4.2-2x9AW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.25 X'±2'		单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.20 .X'±1'		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15 .XX'±0.5'		版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10 .XXX'±0.5'					